

## Precision Dial Calipers

**Roebuck**



These calipers have hardened stainless steel bodies, with satin chrome finish. Four way measurement for outside, inside, depth and step. The calipers in-

corporate a thumb roll for easy adjustment plus knurled locking screw.

490468

| Capacity (in) | Capacity (mm) | Graduations | Jaws  | Order Code      | Price Each |
|---------------|---------------|-------------|-------|-----------------|------------|
| 6             | -             | 0.001in     | 1.6in | <b>137-5965</b> |            |
| -             | 150           | 0.02mm      | 40mm  | <b>137-5845</b> |            |
| 8             | -             | 0.001in     | 1.9in | <b>137-6083</b> |            |
| 12            | -             | 0.001in     | 2.5in | <b>137-6084</b> |            |
| -             | 200           | 0.02mm      | 48mm  | <b>137-5977</b> |            |
| -             | 300           | 0.02mm      | 63mm  | <b>137-5978</b> |            |