

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0510150800](#)  
**Status:** **Active**  
**Overview:** [Board-in Connectors](#)  
**Description:** 2.00mm Pitch, Board-In Crimp Housing, Vertical, 8 Circuits, Natural

**Documents:**

<a href="#">3D Model</a>	<a href="#">Packaging Specification 510159100-EPK-100 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification 510159200-SPK-200 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification PS-51015-002-001 (PDF)</a>	

**General**

Product Family	Crimp Housings
Series	<a href="#">51015</a>
Application	Signal, Wire-to-Board
Overview	<a href="#">Board-in Connectors</a>
Product Name	Board-in
UPC	800753749269


**Physical**

Circuits (maximum)	8
Color - Resin	Natural
Gender	N/A
Glow-Wire Capable	No
Material - Resin	Nylon
Net Weight	151.000/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Stackable	No
Temperature Range - Operating	-40° to +105°C

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	510159100-EPK-100, 510159200-SPK-200
Product Specification	PS-51015-002-001
Sales Drawing	SD-51015-XX00



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)4578-DC (25  
June 2020)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[51015 Series](#)

**Use With**

[50034](#)