

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0351510414**
Status: **Active**
Overview: VersaBlade Wire-to-Wire Connector System
Description: VersaBlade Hybrid Plug Housing, 4 Circuits, Positive Lock, Blue

Documents:

<u>Drawing (PDF)</u>	<u>Application Specification 351500000ASKOR-000 (PDF)</u>
<u>3D Model</u>	<u>Packaging Specification PK-35151-005-001 (PDF)</u>
<u>3D Model (PDF)</u>	<u>Datasheet (PDF)</u>
<u>Product Specification PS-35150-003-001 (PDF)</u>	<u>Brochure (PDF)</u>
<u>Application Specification 351500000ASENG-000 (PDF)</u>	<u>RoHS Certificate of Compliance (PDF)</u>

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	<u>35151</u>
Application	Power, Wire-to-Wire
Overview	<u>VersaBlade Wire-to-Wire Connector System</u>
Product Name	VersaBlade
UPC	800754834728

Physical

Circuits (maximum)	4
Color - Resin	Blue
Flammability	94V-0
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	3.746/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	6.20mm
Pitch - Termination Interface	6.20mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +120°C

Material Info

Reference - Drawing Numbers

Application Specification	351500000AS_ENG-000, 351500000AS_KOR-000
Packaging Specification	PK-35151-005-001
Product Specification	PS-35150-003-001
Sales Drawing	SD-35151-0410



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

35151 Series

Mates With

VersaBlade Receptacle Housing 35150

VersaBlade Multi-Module 2-3-4
Receptacle Housing 35524 , 2026500909

Use With

VersaBlade Crimp Terminals 35746 (ckt 1), 35748 (ckt 2), 35745 (ckt 3), 35747 (ckt 4)
VersaBlade TPA 351500290 , 351500292 , 351500293 , 351500294