

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0459854912](#)  
**Status:** **Active**  
**Overview:** [EXTreme LPHPower Connectors](#)  
**Description:** EXTreme LPHPower Header, Right-Angle, 4 Power Contacts, Select Gold (Au) Plating, for 3.18mm Thick PC Board, with Guide

**Documents:**

<a href="#">3D Model</a>	<a href="#">Packaging Specification PK-45984-001-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Symbol Footprint Data SYM-45985-4912 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification PS-45984-001-001 (PDF)</a>	



Series image - Reference only

**Agency Certification**

CSA	LR19980
UL	E29179

**General**

Product Family	PCB Headers
Series	<a href="#">45985</a>
Application	Board-to-Board, Power
Comments	4 Power Blades
Overview	<a href="#">EXTreme LPHPower Connectors</a>
Product Name	EXTreme LPHPower
UPC	800756694870

**Physical**

(p)ower-(s)ignal Configuration	4p - 0s
Breakaway	No
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Durability (mating cycles max)	250
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	None
Lock to Mating Part	No
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	4.795/g
Number of Rows	2
Orientation	Right Angle
PC Tail Length	4.50mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	3.18mm
Packaging Type	Tray
Pitch - Mating Interface	12.00mm
Pitch - Termination Interface	2.00mm, 2.50mm
Plating min - Mating	0.762µm
Plating min - Termination	3.810µm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Closed Ends

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)4578-DC (25  
June 2020)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[45985](#) Series

**Mates With**

[45984](#) EXTreme LPHPower PCB  
Receptacles

Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole
<b>Electrical</b>	
Current - Maximum per Contact	30.0A
Voltage - Maximum	250V AC (RMS)/DC
<b>Solder Process Data</b>	
Duration at Max. Process Temperature (seconds)	015
Lead-free Process Capability	SMC&WAVE
Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	230
<b>Material Info</b>	
<b>Reference - Drawing Numbers</b>	
Packaging Specification	PK-45984-001-001
Product Specification	PS-45984-001-001
Sales Drawing	SD-45985-102-001
Symbol/Footprint Data	SYM-45985-4912

This document was generated on 08/11/2020

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**