



Pressure Pro Intensive Deep Cleaner RM 750

Powerful deep cleaner effectively removes the most stubborn stains, such as oil, grease, soot, blood and proteins. Low foam production. Particularly suited for floor cleaning by machine and for processing with hard surface cleaners. NTA free.



NTA-free



Properties

- Intensive basic cleaner for use with high-pressure and floor cleaning units
- For thorough cleaning of heavily soiled industrial floor coverings
- Dissolves heavy oil, grease and mineral stains
- Effective quickly
- Low-foam formulation
- Especially productive
- Tensides biodegradable in accordance with EEC 648/2004
- Rapidly separates oil/water in the oil separator (easy to separate=asf)
- NTA free

Areas:

- | | |
|-----------------------------------|--|
| Agriculture: | Transport and transportation equipment |
| Car dealership and garage: | Car/engine wash |
| Car dealership and garage: | Parts cleaning |
| Building Industry: | Transport and transportation equipment |
| Contract cleaning: | Floor cleaning |
| Industry: | Surface degreasing |

Application

- High-pressure washers
- Scrubber-dryers
- Manual

pH

13.7
in concentrate



	Part number
10 l	6.295-539.0
200 l	6.295-540.0

Application:**High-pressure washers**

- Apply primary mixture with fresh water.
- Set the dosage and temperature on the device
- 1-80°C processing temperature.
- Clean object.
- Rinse surface well with clear water.

Scrubber-driers - deep cleaning

- Combine the product with the appropriate dosage and fresh water.
- Allow to soak.
- Reaction time 10-15 minutes, depending on the degree of soiling.
- Wet object completely with product.
- Clean the surface in overlapping sections.
- Neutralise with clear water.

Manual

- Combine the product with the appropriate dosage and fresh water.
- Allow to soak.
- Reaction time 10-15 minutes, depending on the degree of soiling.
- Wet object completely with product.
- Incorporate the cleaning fluid.
- Neutralise with clear water.

Directions for use:

- Test on an inconspicuous part for material compatibility.
- Do not let the cleaning solution dry out.

Further information:

- Material Safety Data Sheet (MSDS)

Dosage and yield:

Content:	Cleaning method:	Primary mixture:	Dosage:	Contamination:	Productivity:
1000 ml	High-pressure washers	1+3	1-5 %	heavy	270 m ²
1000 ml	Scrubber-driers - stripping		10-50 %	heavy	110 m ²
1000 ml	Scrubber-driers - deep cleaning		5-50 %	heavy	370 m ²
1000 ml	Manual		5-50 %	heavy	120 m ²

Please contact us for more information:

Kärcher UK Ltd

Kärcher House
Brookhill Way
Banbury
Oxon OX16 3ED