

HSS Counterbores

Roebuck



- 3 Flute capscrew counterbores
- Straight shank
- Available individually or in a set
- Set supplied in a metal index case with sizes individually marked

490545

Cap screw dia.	Cutter dia. (mm)	Pilot dia. (mm)	Shank dia. (mm)	Order Code	Price Each
M3-M10	Various	Various	Various	137-5996	
M3	6.0	3.4	5.0	137-5898	
M4	8.0	4.5	5.0	137-5899	
M5	10.0	5.5	8.0	137-5900	
M6	11.0	6.6	8.0	137-5997	
M8	15.0	9.0	12.5	137-5998	
M10	18.0	11.0	12.5	137-6089	
M12	20.0	14.0	12.5	137-5999	