


**Features**

- 2 RS232 Serial Ports
- Massive 128 byte transmit and receive FIFO on each port
- PCMCIA Bus - Fully Plug & Play auto configuring interrupt and address
- Sample Programs, Test & Terminal software - all with source code
- Ruggedised Cable

**Specifications**

- Ports: 2 x RS232
- UART: 16950
- Line Drivers: 1 Mbit
- Baud rates: Up to 921,600
- Data Bits: 5, 6, 7 or 8
- Stop bits: 1 or 2
- Parity: odd, even, none, mark or space
- Power: 210mA @ 5V  
20mA @ 12V
- Size: PCMCIA Type II

# RUGGEDISED PCMCIA 2 Port RS232

**Description**

A PCMCIA type II card providing two independent RS232 serial ports. The megabaud data transfer rates and the 128 byte deep FIFOs, coupled with 1Mbit/s line drivers deliver uncompromising performance on your laptop PC. Being mobile no longer limits your options.

**BRAINBOXES PCMCIA CARDS CREATE TRUE COM PORTS**
**Ruggedised**

Brainboxes ruggedised PCMCIA card ensures secure reliable connectivity between your laptop and any attached serial device. Our ruggedised card provides a robust cable that is locked to the serial card during manufacture preventing any possible break in connection.

**Software**

Serial Solutions CD contains support for Windows XP, Windows 2000, Windows Millennium, Windows 9x & Linux.

Windows XP & Windows 2000 signed drivers.

For details of RS232, RS422 or RS485 Standards see:  
[www.brainboxes.com/standards](http://www.brainboxes.com/standards)

**LIFE TIME SUPPORT  
3 YEAR WARRANTY**


**ORDER**

**Description**  
PCMCIA DUAL RS232 RUGGEDISED

**Code**  
PM-132