

# 9885

**Max. 15 W**

## AC/DC DESKTOP REGULATED

- Max. 15 W output power
- Universal input voltage
- 3-pin IEC 320 mains connector
- UL approved
- Compliance with relevant worldwide safety standards
- Exchangeable output plugs, providing:
  - reduced stocking requirements
  - short delivery lead times
  - snap-locks for added safety



<b><u>Technical specifications</u></b>	
Input voltage:	90 - 264 VAC.
Max. output power:	15 W.
Load regulation:	± 5%
Line regulation:	± 0.5% maximum at full load.
Switch frequency:	47-63 kHz.
Inrush current:	<30 A (230 VAC) at 25°C cold start.
Hold up time:	> 5 ms.
Temperature range	
* Operating:	-0°C to +70°C.
* Storage:	-40°C to +85°C.
Derating:	Derated from 100% at +40°C linearly to 50% at +70°C.
Ripple:	1% p-p max..
Efficiency:	> 70% at max. load.
Current limiting:	Yes.
Overvoltage protection:	Yes.
Electrical safety standards:	EN 60950, UL 1950
EMC standards:	
* Emission:	EN 61000-6-3
* Immunity:	EN 61000-6-1
Reliability:	MTBF > 100.000 h at nominal load at 25°C ambient..
Mains connection:	3-pin IEC 320.
Output terminals:	Secondary cable w/exch. Plug
Dimensions (LxWxH):	91 x 38 x 36 mm (without plug).
Weight:	165 g

Some technical specifications may differ for other models and voltage versions.

### Survey of voltage versions

Output voltage (VDC) ±5%	Load current (A)	Output power (W)
5	2,4	12
9	1,6	14,4
12	1,25	15
24	0,625	15

07032006

**www.mascot.no**  
**sales@mascot.no**

**Phone:**  
**Fax:**

**Main Office**  
PO Box 177  
N-1601 FREDRIKSTAD  
NORWAY  
+47 69 36 43 00  
+47 69 36 43 01

**Mascot UK**  
PO Box 1560, Andover  
SP11 8QZ HAMPSHIRE  
UK  
+44 (0)1264 357177  
+44 (0)1264 364055

**Mascot DE-AT-CH-BENELUX**  
Hirschbergstr. 28/7  
D-74838 LIMBACH  
GERMANY  
+49 6287 95140  
+49 6287 95141

Tettnanger Str. 52  
D-88239 WANGEN  
GERMANY  
+49 7528 951677  
+49 7528 951678

**Mascot France**  
38 rue Leo Lagrange  
94270 Le Kremlin Bicêtre  
FRANCE  
+33 1 46 58 71 85  
+33 1 46 58 71 85