

## 9886 Max. 24 W

### AC/DC DESKTOP REGULATED

- Max. 24 W output power
- Universal input voltage
- 3-pin IEC 320 mains connector
- Compliance with relevant worldwide safety standards
- Exchangeable output plugs, providing:
  - reduced stocking requirements
  - short delivery lead times
  - snap-locks for added safety



<b>Technical specifications</b>	
<i>Input voltage:</i>	90 - 264 VAC.
<i>Max. output power:</i>	24 W.
<i>Load regulation:</i>	± 5%
<i>Line regulation:</i>	± 0.5% maximum at full load.
<i>Switch frequency:</i>	47-63 kHz.
<i>Inrush current:</i>	<30 A (230 VAC) at 25°C cold start.
<i>Hold up time:</i>	> 16 ms.
<i>Temperature range</i>	
* <i>Operating:</i>	-0°C to +70°C.
* <i>Storage:</i>	-40°C to +85°C.
<i>Derating:</i>	Derated from 100% at +40°C linearly to 50% at +70°C.
<i>Ripple:</i>	1% p-p max..
<i>Efficiency:</i>	> 70% at max. load.
<i>Current limiting:</i>	Yes.
<i>Overvoltage protection:</i>	Yes.
<i>Electrical safety standards:</i>	EN 60950, UL 1950
<i>EMC standards:</i>	
* <i>Emission:</i>	EN 61000-6-3
* <i>Immunity:</i>	EN 61000-6-1
<i>Reliability:</i>	MTBF > 100.000 h at nominal load at 25°C ambient..
<i>Mains connection:</i>	3-pin IEC 320.
<i>Output terminals:</i>	Secondary cable w/exch. Plug
<i>Dimensions (LxWxH):</i>	106 x 65 x 30 mm (without plug).
<i>Weight:</i>	215 g

#### Survey of voltage versions

<i>Output voltage (VDC) ±5%</i>	<i>Load current (A)</i>	<i>Output power (W)</i>
9	2,44	22
12	2,00	24
24	1,00	24

07032006

**www.mascot.no**  
**sales@mascot.no**

**Phone:**  
**Fax:**

**Main Office**  
PO Box 177  
N-1601 FREDRIKSTAD  
NORWAY  
+47 69 36 43 00  
+47 69 36 43 01

**Mascot UK**  
PO Box 1560, Andover  
SP11 8QZ HAMPSHIRE  
UK  
+44 (0)1264 357177  
+44 (0)1264 364055

**Mascot DE-AT-CH-BENELUX**  
Hirschbergstr. 28/7  
D-74838 LIMBACH  
GERMANY  
+49 6287 95140  
+49 6287 95141

Tettnanger Str. 52  
D-88239 WANGEN  
GERMANY  
+49 7528 951677  
+49 7528 951678

**Mascot France**  
38 rue Leo Lagrange  
94270 Le Kremlin Bicêtre  
FRANCE  
+33 1 46 58 71 85  
+33 1 46 58 71 85