



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
J	-	A REDRAWN	ECR-05-000767	26MAY2005	Y.Y D.M



- JUMPER LENGTH "L" IS FROM 12.7 MIN. TO 609.6 MAX.
- RECOMMENDED THROUGH HOLE DIA DIMENSION FOR P.C.BOARD: $\phi 0.71 \pm 0.025$
THROUGH HOLE PITCH TOLERANCE: ± 0.127
- ANOTHER SPECIFICATION SHOULD BE ESTABLISHED IN CASE OF DEVIATION FROM THIS SPECIFICATION.
- WHEN N IS GREATER THAN 31, PCN INSERTION IS SUBJECT TO HAVE DIFFICULTY.
- DIMENSIONS OF LEAD POSITION ARE FOOT OF LEAD.

127	76.2	15	-	NOT AVAILABLE	-
			-	NOT AVAILABLE	-
			-	NOT AVAILABLE	-
			-	NOT AVAILABLE	-
			FSN-13A-15=JUMPER	4-1437132-9	A
P	L	N	PART NAME	PN	TYPE

- ジャンパー長さ"L"は、最小12.7から、最大609.6まで。
- プリント基板スルーホール径： $\phi 0.71 \pm 0.025$ また、スルーホールピッチ公差は、 ± 0.127 である。(推奨)
- 本仕様から逸脱する場合は、必ず仕様打合わせを行うこと。
- N31以上製品は、プリント基板挿入性が悪い場合がある。
- リード位置寸法は、リード根元部寸法とする。

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	Y.YAMADA	26MAY2005		Tyco Electronics AMP K.K. Kawasaki, Japan
CHK	D.MITSUGI	26MAY2005		
APVD	D.MITSUGI	26MAY2005	NAME FLEX STRIP JUMPER NOMEX P1.27L76.2N15 フレックスストリップ ジャンパー ノーメックス P1.27L76.2N15	
PRODUCT SPEC	製品規格	108-78002	SIZE	A3
APPLICATION SPEC	取付適用規格	-	CAGE CODE	00779
WEIGHT	-	-	DRAWING NO	C-4-1437132-9
CUSTOMER DRAWING			RESTRICTED TO	-
SCALE			尺度	-
SHEET			1	OF 1
REV			A	