

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2138141108](#)
Status: **Active**
Overview: [Mega-Fit Power Connectors](#)
Description: Mega-Fit Plug Housing, Single Row, 8 Circuit, UL 94V-0, Glow-Wire Capable, Panel Mount

Documents:

Drawing (PDF)	Packaging Specification 2138140001-PK-000 (PDF)
Product Specification 1054171000-PS-000 (PDF)	Datasheet (PDF)
Application Specification 768232000-AS-000 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Housings
Series	213814
Application	Power, Wire-to-Wire
Overview	Mega-Fit Power Connectors
Product Name	Mega-Fit
UPC	193264466245

Physical

Circuits (maximum)	8
Color - Resin	Black
Gender	Plug
Glow-Wire Capable	Yes
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	6.050/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	5.70mm
Pitch - Termination Interface	5.70mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C, -40° to +120°C

Material Info

Reference - Drawing Numbers

Application Specification	768232000-AS-000
Packaging Specification	2138140001-PK-000
Product Specification	1054171000-PS-000
Sales Drawing	2138140001-SD-000



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[213814 Series](#)

Mates With

Mega-Fit Receptacle Housing [200456](#)

Use With

Mega-Fit TPA [105415](#)
Mega-Fit Crimp
Terminals [105417](#) , [105418](#)