

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0150140421](#)
Status: **Active**
Overview: Premo-Flex Flat-Flexible Circuit (FFC) Cable Jumpers
Description: 0.25mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 101.60mm Cable Length, Gold (Au) Plating, 21 Circuits

Documents:

[Drawing \(PDF\)](#) [Datasheet \(PDF\)](#)
[Product Specification 1501400001-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable
Series	15014
Crimp Quality Equipment	Yes
Overview	<u>Premo-Flex Flat-Flexible Circuit (FFC) Cable Jumpers</u>
Product Name	Premo-Flex FFC Jumper
UPC	191130093304

Physical

Cable Length	101.60mm
Circuits (Loaded)	21
Material - Plating Mating	Gold
Net Weight	1.000/g
Packaging Type	Bag
Pitch - Mating Interface	0.25mm
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable

Electrical

Current - Maximum per Contact	0.2A
Voltage - Maximum	N/A

Material Info

Reference - Drawing Numbers

Product Specification	1501400001-000
Sales Drawing	150140001-000



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[15014 Series](#)

Mates With

Easy-On FFC/FPC Connector [5020782110](#) , [5020782162](#) , [5033002110](#)