

**Connecting elements
H70,0/25**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



For conductors from 10.0 to 185.0 mm² (AWG 7 - 350 MCM)
 tin-plated copper
 dimensional tolerances to DIN 46228 part 1
 • supplied loose in poly-bag

General ordering data

Type	H70,0/25
Order No.	9004230000
Version	Wire-end ferrule, uninsulated, 25 mm
GTIN (EAN)	4008 190 15005 1
Qty.	50 pc(s).
Packaging	loose

Creation date September 7, 2020 10:41:13 AM CEST

Data sheet

Connecting elements H70,0/25

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Net weight	3.49 g
------------	--------

Technical data

Version	uninsulated
---------	-------------

Wire-end ferrules

Collar diameter (D2)	15 mm	Conductor cross-section	70 mm ²
Contact surface diameter (D1)	12.5 mm	L1 in mm	25 mm
Stripping length	25 mm	Wire connection cross section AWG, max.	AWG 2/0

Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
eClass 9.0	27-40-02-01	eClass 9.1	27-40-02-01
eClass 10.0	27-40-02-01	UNSPSC	31-16-31-02

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP

Data sheet

**Connecting elements
H70,0/25**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

