

**Bolt-type screw terminals
WAH 120**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image**Klippon® Connect with stud Technology**

Our stud terminals are an established, robust connection alternative for particularly harsh environments. The extensive accessories and quality workmanship ensure high productivity in planning and installation – and sustainable safety in operation..

General ordering data

Type	WAH 120
Order No.	1064660000
Version	Bolt-type screw terminals, Hood, beige, 41 mm
GTIN (EAN)	4008190100797
Qty.	20 pc(s).

Creation date September 7, 2020 10:35:37 AM CEST

Catalogue status 05.09.2020 / We reserve the right to make technical changes.

Bolt-type screw terminals
WAH 120

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Width	41 mm	Width (inches)	1.614 inch
Height	110.25 mm	Height (inches)	4.341 inch
Depth	34.5 mm	Depth (inches)	1.358 inch
Net weight	15.66 g		

Temperatures

Storage temperature, max.	55 °C	Storage temperature, min.	-25 °C
Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

Material data

Material	Polyamide 66	Colour	beige
UL 94 flammability rating	V-2		

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	Snap-on		

Dimensions

Pitch in mm (P)	42 mm
-----------------	-------

Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
eClass 9.0	27-14-11-92	eClass 9.1	27-14-11-92
eClass 10.0	27-14-11-92	UNSPSC	30-21-18-27

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 1 TERM 16/17 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP
User Documentation	StorageConditionsTerminalBlocks