



Creating Safe Work Solutions During COVID-19

WLS15HCDW0360LS24QP

► WLS15 LOW PROFILE, LOW POWER LED STRIP LIGHT



WLS15 High Intensity Light Strip; Light Diffuse Window; Length: 360 mm

Voltage: 24 V dc; Environmental Rating: IP66; IP67

Color: DW; Cascadable

Euro 4-pin 150 mm (6 in) PVC Pigtail

Part Number: 809885

CERTIFICATIONS



SPECIFICATIONS

Cable Length (m)	2
Housing Style	Linear Strip
Primary Housing Material	Polycarbonate
Illumination	Yes
Mounting Thread	No Thread
Color Input Control	Individual (One wire/color, same number of colors as input wires)
Number of Colors / Segments	1
Product Size (mm)	15



Contact Us

Color Technology	Standard LED
Color Option 1	White
Connection	Pigtail QD
Quick Disconnect Type	M12 (Euro)
Lumens Color 1	750
Color 1 - Wavelength/Color Temp/Coordinates	5000K (Daylight)
Max Current Color (mA)	360
Dimming Option	High-Low-Off
Number of Input Pins/Conductors	4
Supply Voltage	24 V dc
Illuminated Length (LxWxH mm)	286.4
Physical Dimensions (LxWxH or DxH mm)	360.0 x 30.6 x 15.5
Environmental Rating	IP66; IP67
Max Op. Temperature (°C)	50
Min Op. Temperature (°C)	-40
Storage Temp (°C)	-40 to 70
Primary Window Material	Polycarbonate Diffused
Secondary Material	Polyamide
Feature: Hazardous Area	No
Feature: Audible	No
Feature: Cascade	Yes
Feature: Chemical Resistant	No
IO Link	No
Modbus RTU	No
Wireless	No
USB	No


[Contact Us](#)

Pro-Editor Compatible

No

COMPATIBLE PRODUCTS

BRACKET

	<p>LMBWLS15</p> <p>Bracket: For Use with WLS15
Mounting Clip Kit
Contains 3 Brackets</p>
	<p>LMBWLS15-150S</p> <p>Bracket: For Use with WLS15
150 Degree Rotation
Set of Two
Stainless Steel</p>
	<p>LMBWLS15MAG</p> <p>Bracket: For Use with WLS15
Magnetic Mounting Kit
Set of Two
Up to 16 lb Pull</p>

DOUBLE-ENDED CORDSETS

	<p>MQDEC-401SS</p> <p>Euro-style Quick Disconnect Cable
Double-ended 4-pin Male Connector Straight
4-pin Female Connector Straight 0.3 m Length
Chrome plated brass coupling nut</p>
	<p>MQDEC-403SS</p> <p>Euro-style Quick Disconnect Cable
Double-ended 4-pin Male Connector Straight
4-pin Female Connector Straight 0.91 m Length
Chrome plated brass coupling nut</p>
	<p>MQDEC-406SS</p> <p>Euro-style Quick Disconnect Cable
4-pin Straight Connector
2 m (6.5 ft) Length
Double Ended With 1 Female & 1 Male Connector</p>
	<p>MQDEC-412SS</p> <p>Euro-style Quick Disconnect Cable
Double-ended 4-pin Male Connector Straight
4-pin Female Connector Straight 3.7 m Length
Chrome plated brass coupling nut</p>
	<p>MQDEC-420SS</p> <p>Euro-style Quick Disconnect Cable
Double-ended 4-pin Male Connector Straight
4-pin Female Connector Straight 6.1 m Length
Chrome plated brass coupling nut</p>
	<p>MQDEC-430SS</p> <p>Euro-style Quick Disconnect Cable
Double-ended 4-pin Male Connector Straight
4-pin Female Connector Straight 9.1 m Length
Chrome plated brass coupling nut</p>


[Contact Us](#)

MQDEC-450SS

Euro-style Quick Disconnect Cable
Double-ended 4-pin Male Connector Straight
4-pin Female Connector Straight 15 m Length
Chrome plated brass coupling nut

SINGLE-ENDED CORDSETS**MQDC-406**

Euro-style Quick Disconnect Cable
4-Pin Straight Connector
2 m (6.5 ft) in Length
Nickel-plated Brass Coupling Nut

MQDC-406RA

Euro-Style Quick Disconnect Cable
4-Pin Right-Angle Connector
2 m (6.5 ft) in Length
Nickel-plated brass coupling nut

MQDC-415

Euro-style Quick Disconnect Cable
4-Pin Straight Connector
5 m (15 ft) in Length
Nickel-plated Brass Coupling Nut.

MQDC-415RA

Euro-Style Quick Disconnect Cable
4-Pin Right-Angle Connector
5 m (15 ft) in Length
Nickel-plated brass coupling nut

MQDC-430

Euro-style Quick Disconnect Cable
4-Pin Straight Connector
9 m (30 ft) in Length
Nickel-plated Brass Coupling Nut

MQDC-430RA

Euro-Style Quick Disconnect Cable
4-Pin Right-Angle Connector
9 m (30 ft) in Length
Nickel-plated brass coupling nut

MQDC-450

Euro-Style Quick Disconnect Cable
4-Pin Straight Connector
15 m (50 ft) in Length
Nickel-plated Brass Coupling Nut

MQDC-450RA

Euro-Style Quick Disconnect Cable
4-Pin Right-Angle Connector
15 m (50 ft) in Length
Nickel-plated brass coupling nut

MISCELLANEOUS**LMBWLS15TD**

Two strips of 3M Dual Lock adhesive



Contact Us

LMBWLS15TF

Two strips of double sided foam urethane tape

LC65 LED DIMMING MODULE**LC65P2T**

LED Dimmer Module; 2 -Wire
Pulse Width Modulation
12-30 V dc; 4 Amps
Terminal Connection

PSD-24-4

DC Power Supply - Desktop Style
Input: 90-264 V ac 50/60 Hz: 1.8 m (6 ft) US Style outlet plug
Output: 24 V dc 4 A: 2 m (6.5 ft) Euro 4-pin Connector
UL Listed Class 2



Banner Engineering Corp. | 9714 Tenth Avenue North | Minneapolis, MN 55441 | United States of America



Contact Us