

Hex Nut - Dynabolt

Zinc-Plated



- Suitable for concrete, brickwork and dense concrete blocks
- When tightened, the bolt is drawn with the tapered base through the sleeve, expanding it against surrounding material to ensure a firm grip

- Thin-walled sleeve anchor
- Integral nut and washer

| Anchor Hole ∅ | Thread Size | Fastens Material Up To | Min. Hole Depth | Mfrs. List No. | Order Code |
|------------------|-------------|---------------------------|--------------------|----------------|------------|
| 6 | M4.5 | 5 | 25 | DP0640 | 705-8330 |
| 8 | M6 | 8 | 40 | DP0840 | 705-8342 |
| 8 | M6 | 30 | 40 | DP0865 | 705-8354 |
| 8 | M6 | 55 | 40 | DP08090 | 705-8366 |
| 10 | M8 | 10 | 45 | DP10050 | 705-8378 |
| 10 | M8 | 20 | 45 | DP10075 | 705-8380 |
| 12 | M10 | 20 | 55 | DP12070 | 705-8391 |
| 12 | M10 | 50 | 55 | DP12100 | 705-8408 |
| 16 | M12 | 15 | 55 | DP16065 | 705-8410 |
| 16 | M12 | 55 | 60 | DP16110 | 705-8421 |

FAS29/203966

| | Max. Material Thickness | Order Code | Price Each |
|------|----------------------------|-----------------|------------|
| M4.5 | 5 | 705-8330 | |
| M6 | 8 | 705-8342 | |
| | 30 | 705-8354 | |
| | 55 | 705-8366 | |
| M8 | 10 | 705-8378 | |
| | 20 | 705-8380 | |
| M10 | 20 | 705-8391 | |
| | 50 | 705-8408 | |
| M12 | 15 | 705-8410 | |
| | 55 | 705-8421 | |