

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2164001031](#)
Status: **Active**
Overview: [Mega-Fit Power Connectors](#)
Description: Mega-Fit Female-to-Mega-Fit Female Off-the-Shelf (OTS) Cable Assembly, Single Row, 150.00mm Length, Tin Plated, 3 Circuits, Black

Documents:

[Drawing \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	216400
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Mega-Fit-to-Mega-Fit
Overview	Mega-Fit Power Connectors
Product Name	Mega-Fit
Type	Discrete Wire Assembly
UPC	193264723447

Physical

Cable Length	150.00mm
Circuits (Loaded)	3
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	High Conductivity Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	27.787/g
Number of Rows	1
Pitch - Mating Interface	5.70mm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	4.06mm max.
Wire Size AWG	12
Wire/Cable Type	UL 1015


Electrical

Current - Maximum per Contact	25.0A
Voltage - Maximum	600V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Sales Drawing	2164001031-000
---------------	----------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[216400 Series](#)

Mates With

Mega-Fit Header [200241](#)
Mega-Fit Plug
Housing [213814](#) , [213815](#)