

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2121320002](#)
Status: **Active**
Overview: [Pico-EZmate and Pico-EZmate Slim Wire-to-Board Connector Systems](#)
Description: [1.00mm Pitch Pico-EZmate Plus Receptacle Housing, Single Row, 2 Circuits, Black](#)

Documents:

[Drawing \(PDF\)](#) [Datasheet \(PDF\)](#)
[Product Specification 2121320000-PS-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification 2121329200-SPK-200 \(PDF\)](#)

General

Product Family [Crimp Housings](#)
Series [212132](#)
Application [Signal, Wire-to-Board](#)
Overview [Pico-EZmate and Pico-EZmate Slim Wire-to-Board Connector Systems](#)

Product Name [Pico-EZmate Plus](#)
UPC [193264124626](#)

Physical

Circuits (maximum) [2](#)
Color - Resin [Black](#)
Gender [Receptacle](#)
Glow-Wire Capable [No](#)
Keying to Mating Part [None](#)
Lock to Mating Part [Yes](#)
Material - Resin [Polyamide](#)
Net Weight [7.100/mg](#)
Number of Rows [1](#)
Packaging Type [Bag](#)
Panel Mount [No](#)
Pitch - Mating Interface [1.00mm](#)
Polarized to Mating Part [Yes](#)
Temperature Range - Operating [-40° to +105°C](#)

Material Info

Reference - Drawing Numbers

Packaging Specification [2121329200-SPK-200](#)
Product Specification [2121320000-PS-000](#)
Sales Drawing [2121320000-SD-000](#)



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[212132 Series](#)

Mates With

[Pico-EZmate Plus PCB Header 212134](#)