



PSG3362

A/V to HDMI+Stereo Converter

Please read these instructions carefully before use and retain for future reference.

INTRODUCTION

- The AV TO HDMI converter is a universal converter for analog composite input to HDMI 1080p (60HZ) output.
- The analog to digital conversion in this module employs 10 bits maximal 162MSPS sampling, black/white level expansion, color transition improvement, dynamic range expansion, blue stretch, auto-detect and auto-convert the composite signal to 1080p(60HZ) output. Making video come alive, delivering the sharpest, most realistic HD visuals available.

FEATURES

- No need to install drivers, portable, flexible, plug and play;
- Provide advanced signal processing with great precision, colors, resolutions, and details;
- Support PAL, NTSC3.58, NTSC4.43, SECAM, PAL/M, PAL/N standard TV formats input;
- Support Up Scaler;
- Support HDMI 1080p or 720p output.

PACKAGE CONTENTS

Before attempting to use this unit, please check the packaging and make sure the following items are contained in the shipping carton:

- AV to HDMI Converter-----1PCS
- 5V 1A Power adapter-----1PCS
- User Manual-----1PCS

SPECIFICATIONS

- Input ports-----3xRCA (Yellow, White, Red)
- Output port-----1x3.5mm Stereo, 1xHDMI
- Dimensions (mm)-----73(L) x60.5(W) x22.5(H)
- Wight (g)-----90
- Composite input -----PAL, NTSC3.58, NTSC4.43, SECAM, PAL/M, PAL/N
- HDMI output-----1080p60Hz, 720p/60Hz

PANEL DESCRIPTIONS

Please study the panel drawings below and become familiar with the signal input(s), output(s) and power requirements.



- CVBS -----CVBS input
- L/R -----Audio input
- DC 5V-----5V power input
- PWR -----Power indicator
- 720P/1080P-----720P/1080P switch
- HDMI -----HDMI output
- Stereo Out -----Audio output

CONNECTION DIAGRAM

Before installation, please make sure all devices you wish to connect have been turned off.



- Connect the AV input of this product to the Converter.
- Connect the HDMI output from converter to the this Displayer. (Input cables are optional)
- Insert the DC side of 5V power supply into this product and then connect the AC side of the power supply into the wall outlet.
- Power on all connected devices, Choose the input of the display device to its HDMI channel.
- The image does not need to be adjusted, the Converter will position it automatically, the user may adjust the horizontal position under some extreme condition.

Attention: Insert / Extract cable gently.

INSTALLATION AND PRECAUTIONS

- When using electrical appliances basic safety precautions should always be followed.
- Check that the voltage indicated on the rating plate corresponds with that of the local network before connecting the PSU to the mains supply.
- Keep the equipment away from moisture or excessive heat.
- There are no user serviceable parts inside.
- Take care when connecting or disconnecting cables.



INFORMATION ON WASTE DISPOSAL FOR CONSUMERS OF ELECTRICAL & ELECTRONIC EQUIPMENT.

When this product has reached the end of its life it must be treated as Waste Electrical & Electronic Equipment (WEEE). Any WEEE marked products must not be mixed with general household waste but kept separate for the treatment, recovery and recycling of the materials used. Contact your local authority for details of recycling schemes in your area.

Made in China, PR2 9PP
Man Rev 1.0