



Image is for illustrative purpose only

Snap Fit Bushing - Panel Thickness Range 0.8 - 3.2 mm | 0.031 - 0.125 in ; Approximate Cable Holding Diameter 6.4 mm | 0.250 in

Item code: **22MP06254**

This open snap-fit bush can be installed tool-free in to panels with little effort to provide protection against rough panel hole edges. It is manufactured with heat stabilized UL94 V-2 rated material.

Specifications

Approximate Cable Holding Diameter	0.250 in
---	----------

Compatible Hole Diameter	0.625 in
Head Diameter	0.718 in
Inside Diameter	0.250 in
Maximum Operating Temperature	185 °F
Maximum Panel Thickness	0.125 in
Minimum Operating Temperature	-40 °F
Minimum Panel Thickness	0.031 in
Operating Temperature Range	-40 - 185 °F
Overall Height	0.406 in
Panel Thickness Range	0.031 - 0.125 in
Bushing Type	Closed
Color	Black
Full Material	Nylon 6
Material	Nylon
Material Flammability Standard	UL94 V-2
Open/Closed	Open
Special Features	Heat-Stabilized