



576TX1

Product no.: 576TX1

Side cutter - tapered head - smooth and precise rounded tips



The jaws of the cutter have straight edges and taper to a point. This head shape allows access to difficult to reach areas but reduces the cutting capacity in comparison to the same size oval head cutter.



[source images](#)

The Perfect Cut - Strong, sharp and precise, every time

The Weller Erem distance cutters are available with fixed and variable cutting lengths. With the distance cutters wires can be cut to the correct length. They are also suitable to fix components. The tips are polished as to prevent board damage.

THE PERFECT CUT

Strong, sharp and precise - every time

- + 1 Million Movements**
Magic Spring™ design enables maximum durability with constant spring force movements
- + Quality**
Uncompromising Swiss quality created to be strong, durable and sharp
- + Precision**
Experience precise cuts from the high-precision screw joint that enables a smooth action with no jaw overlap
- + Strong and Sharp**
Hand-crafted cutting edges for superior strength and sharpness
- + Comfort, Security and Grip**
Ergonomically-shaped handles provide superior comfort and fatigue-free handling with Maximum Opening Stop Technology
- ESD Safe**
Made from ESD-safe material to prevent damage to sensitive components

Swiss Made

weller-tools.com **Weller**
Erem





Technical Data

Length mm	115
Length of cutting edges mm	10
Head width mm	11
Head thickness mm	6
Head length mm	18.5
Max. cutting capability – hard wire mm	Ø 0,4
Weight in oz	2.363
Length of cutting edges Inches	0.394
Head width Inches	0.433
Head thickness Inches	0.236
Head length Inches	0.728
ESD-safe	on
Cut	Flush
Max. cutting capability – medium hardness mm	Ø 0,5
Max. cutting capability – copper wire mm	Ø 1,0
Length inches	4.528
Weight in g	67
Erem applications	Medical technology