

32 Port USB Fast Charger



TIGER PART: TGR-32P-USB

Features:

- 32 ports x 1.5 amp fast charging outputs
- Universal 100-240vac input voltage
- Everything needed supplied in the box
- Level VI efficiency
- Approved to latest 62368-1 safety standards



The Tiger Power range of USB chargers are safety approved and highly reliable, meeting latest level VI energy efficiency legislation. The TGR-32P-USB model has 32 ports, allowing for a whole office or classroom to charge and sync their device at the same time via the 1.5 amp outputs. Suitable for a wide range of applications.

Part number (no mains cable included):	TGR-32P-USB-NC
Part number (Supplied with separate UK cable) :	TGR-32P-USB
Part number (European cable):	TGR-32P-USB-EU
Input voltage:	100-240vac (90-264vac max.)
Input frequency:	47 - 63Hz
Output voltage:	5vdc
Current:	1.5 amps max. x 32 ports
Power :	32 Ports x 1.5A max. Fast Charging (240W max)
Powered by:	2 x 12vdc 10A 120W power supplies (supplied)
Dimensions:	395 x 80 x 23.5mm
Weight:	2250g
AC cord length (where supplied):	1.8 to 2 metres (depending on version)
DC cord length:	Not applicable
DC connector:	USB type A
Polarity:	Standard
Efficiency:	89%
Input current RMS Max.:	2.0A
Inrush Current at 230vac:	120A max. at 220vac cold start, max. load
Load regulation:	+ / - 5%
Safety approval:	62368-1
M.T.B.F:	50,000 hours (MIL-HDBK-217F) at 25 degrees C
Operating temperature:	0°C to + 40°C

TIGER POWER PRODUCTS – QUALITY & RELIABILITY

This specification is not for general release or circulation. Tiger Power reserves the right to make changes to spec. or product without notice or liability.

32 Port USB Fast Charger



TIGER PART: TGR-32P-USB

Supplied in the box

- 32 Port USB Hub
- 2 x 12VDC power supplies & UK mains leads
- Data Cable



TIGER POWER PRODUCTS – QUALITY & RELIABILITY

This specification is not for general release or circulation. Tiger Power reserves the right to make changes to spec. or product without notice or liability.