

## Han-Eco 10B-Cover-for DL-w. cord-HBM-HSM



Image is for illustration purposes only. Please refer to product description.

Part number	19 43 010 5425
Specification	Han-Eco 10B-Cover-for DL-w. cord-HBM-HSM
HARTING eCatalogue	<a href="https://b2b.harting.com/19430105425">https://b2b.harting.com/19430105425</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Eco® B
Type of hood/housing	Protection cover
Description of hood/housing	for bulkhead mounted housings for surface mounted housings

### Version

Locking type	Double locking lever
Size	10 B

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP66

### Material properties

Material (hood/housing)	Polyamide (PA) Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No



Pushing Performance

## Material properties

REACH ANNEX XIV substances No

REACH SVHC substances No

## Specifications and approvals

Specifications	IEC 61984
	EN 45545-2 R22: HL1, HL2, HL3
	EN 45545-2 R23: HL1, HL2, HL3
	EN 45545-2 R24: HL1, HL2, HL3

## Commercial data

Packaging size	1
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440208 Cap for industrial connectors