


TE Internal #: T4161320008-007 M8/M12 Cable Assemblies, Sensor/Actuator, 8 Positions, A M8 /M12 Cable Assembly Keying, Receptacle, M12 Pigtail, Straight View on TE.com >



Cable Assemblies > Copper Cable Assemblies > M8/M12 Cable Assemblies > M12 A-CODE FEMALE STRT SINGLE END CABLE



M8/M12 Application Type: Sensor/Actuator

Number of M8/M12 Cable Assembly Positions: 8

M8/M12 Cable Assembly Keying: A

M8/M12 Cable Assembly Connector Type: Receptacle

M8/M12 Cable Assembly Type: M12 Pigtail

All M12 A-CODE FEMALE STRT SINGLE END CABLE (140)

Features

Product Type Features

| LED | Without |
|---|----------------|
| Cable Type | PUR |
| Product Type | Cable Assembly |
| Assembly Type | Pigtail |
| M8/M12 Cable Assembly Connector Type | Receptacle |
| M8/M12 Cable Assembly Type | M12 Pigtail |
| M8/M12 Cable Assembly Shielded | Yes |
| Configuration Features | |
| Number of M8/M12 Cable Assembly Positions | 8 |
| M8/M12 Cable Assembly Keying | A |
| M8/M12 Cable Assembly Configuration | Single Ended |
| Electrical Characteristics | |
| Operating Voltage | 30 VDC |

T4161320008-007

M8/M12 Cable Assemblies, Sensor/Actuator, 8 Positions, A M8/M12 Cable Assembly Keying, Receptacle, M12 Pigtail, Straight



Body Features

| Cable Exit Angle | Straight |
|--|-----------------|
| Conductor Material | Copper Alloy |
| Cable Jacket Color | Gray |
| Mechanical Attachment | |
| Screw & Hole Thread Size | M12 |
| M8/M12 Cable Assembly Mounting Angle | Straight |
| Housing Features | |
| M8/M12 Cable Assembly Housing Material | GF Nylon |
| Dimensions | |
| Cable Assembly Length | 10000 mm |
| Operation/Application | |
| M8/M12 Application Type | Sensor/Actuator |
| Packaging Features | |
| Packaging Method | Bag |
| Packaging Quantity | 2 |

Other

Yes

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU

EU ELV Directive 2000/53/EC

China RoHS 2 Directive MIIT Order No 32, 2016

EU REACH Regulation (EC) No. 1907/2006

Halogen Content

Solder Process Capability

Compliant with Exemptions

Compliant with Exemptions

Restricted Materials Above Threshold

Current ECHA Candidate List: JUN 2020

(209)

Candidate List Declared Against: JAN 2020

(205)

SVHC > Threshold:

Pb (4% in Pb-Alloy in Copper)

Article Safe Usage Statements:

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Not Yet Reviewed for halogen content

Not applicable for solder process capability

T4161320008-007

M8/M12 Cable Assemblies, Sensor/Actuator, 8 Positions, A M8/M12 Cable Assembly Keying, Receptacle, M12 Pigtail, Straight




Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



Customers Also Bought



T4161320008-007

M8/M12 Cable Assemblies, Sensor/Actuator, 8 Positions, A M8/M12 Cable Assembly Keying, Receptacle, M12 Pigtail, Straight





Documents

Product Drawings RPC-M12-FS-8CON-PUR-10.0SH

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_T4161320008-007_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_T4161320008-007_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_T4161320008-007_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Datasheets & Catalog Pages M8 / M12 Connector System Catalog

English

Product Specifications Application Specification

English