



884E

Product no.: T884E

Side cutter - pointed relieved head




This is the narrowest head shape.



The underside is relieved and facilitates optimum access even to extremely hard-to-reach areas.



The underside is relieved and facilitates optimum access even to extremely hard-to-reach areas.



source images

The Perfect Cut - Strong, sharp and precise, every time

The Weller Erem Series 800 Maxi is a range of maxi-sized precision cutters for general cutting applications in electronics to cut large wire diameters. The cutters are made from high grade tool steel with cutting edges hardened to 63-65HRC. The precision cutters have a nonreflecting surface, are ESD safe and resharpenable.

Type	Type of Cut	Cutting Capacity
------	-------------	------------------

Series 600 Micro & 2600

mm 0,03 0,1 0,2 0,3 0,4 0,5 0,6 0,7 0,8 0,9 1,0 1,1 1,2 1,3 1,4 1,5 1,6 1,7 1,8 1,9 2,0
Inch .0001 .003 .007 .011 .015 .019 .023 .027 .031 .035 .039 .043 .047 .051 .055 .059 .062 .066 .070 .074 .078

	612N 2612N	Semi Flush	
	622N 2622N	Flush	
	622TX	Flush / Carbide	
	632N 2632N	Super Full Flush	
	622NA	Flush	
	622NB 2622NB	Flush	
	676E	Flush	
	776E	Super Full Flush	
	632NCF	Super Full Flush	only for soft materials: silicone, rubber...
	670E	Flush	
	670EP	Flush	
	670EPF	Flush	for micro pitches under 0,5 mm





Technical Data

Length mm	120
Length of cutting edges mm	15
Head width mm	13.5
Head thickness mm	7.2
Head length mm	21
Max. cutting capability – hard wire mm	---
Weight in oz	2.857
Length of cutting edges Inches	0.590
Head width Inches	0.531
Head thickness Inches	0.284
Head length Inches	0.827
ESD-safe	on
Cut	Flush
Max. cutting capability – medium hardness mm	Ø 0,8
Max. cutting capability – copper wire mm	Ø 1,6
Length inches	4.724
Weight in g	81
Erem applications	Microelectronic