


Banner's Call for Parts creates a steady workflow and pinpoints critical issues. [Learn more.](#)

SXA-1215D


▶ PRODUCTS FOR INDUSTRIAL AUTOMATION



Euro-Style Quick Disconnect Cable
 12 Pin Euro-Style Female Connector
 4.57 m (15 ft) in Length
 26 AWG
 Non-Shielded
 Part Number: 810441

SPECIFICATIONS


Number of Contacts	12
Number of Connectors	1
Cable Jacket Material	PVC
Cable Jacket Color	Yellow
Connector Body Material/Color	PUR Black
Outside Cable Diameter (mm)	6
Cordset Length (m)	4.57
Trunk Length (m)	No Trunk
Shield/No Shield	No Shield
Coupling Material/Color	Nickel Plated Brass
Maximum Temp. (°C)	105
Current Rating (A)	2.0

 Offline (Contact Us)

Minimum Temp. (°C)	-40
Voltage Rating (V)	75 V ac/dc
IP Rating	IP67
Primary Connector Type	EURO
Primary Coupling Method	M12 Single Key
Primary Gender	Female
Primary Orientation	Straight
Primary Number of Conductors	12
Primary AWG	26
Secondary Connector Type	Flying Leads
Secondary Number of Conductors	12
Secondary AWG	26
Feature: Hazardous Area	No
Oil/Grease Resistant	No



Banner Engineering Corp. | 9714 Tenth Avenue North | Minneapolis, MN 55441 | United States of America

 Offline (Contact Us)