

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2170640071](#)

**Status:** **Active**

**Overview:**

**Description:** Micro-One Wire-to-Board Header, Right-Angle, 2.00mm Pitch, Single Row, Glow-Wire Capable, 7 Circuits, Tin-Bismuth Plating, Black

**Agency Certification**

UL E29179

**General**

Product Family PCB Headers  
Series [217064](#)  
Application Power, Wire-to-Board  
Overview microone  
Product Name Micro-One  
UPC 195842005648

**Physical**

Breakaway No  
Circuits (Loaded) 7  
Circuits (maximum) 7  
Color - Resin Black  
Durability (mating cycles max) 30  
First Mate / Last Break No  
Glow-Wire Capable Yes  
Lock to Mating Part Yes  
Material - Metal Brass  
Material - Plating Mating Tin-Bismuth  
Material - Resin Polyamide  
Net Weight 1212.672/mg  
Number of Rows 1  
Orientation Right Angle  
PCB Retention Yes  
Packaging Type Embossed Tape on Reel  
Pitch - Mating Interface 2.00mm  
Polarized to PCB Yes  
Temperature Range - Operating -40° to +105°C  
Termination Interface: Style Surface Mount

**Electrical**

Current - Maximum per Contact 4.0A  
Voltage - Maximum 250V AC (RMS)/DC

**Material Info**

**Reference - Drawing Numbers**

Application Specification 2059790000-AS-000  
Packaging Specification 2170649200-SPK-200  
Product Specification 2059790000-PS-000  
Sales Drawing 2170640000-SD-000

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)9139-DC (19  
Jan 2021)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[217064](#) Series

**Mates With**

Micro-One Receptacle Housing [205979](#)