

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2175212124](#)
Status: **Active**
Overview: [Off-the-Shelf Pre-Crimped Leads](#)
Description: Pre-Crimped Lead Mizu-P25 Female-to-Pigtail, Tin (Sn) Plating, 300.00mm Length, 22 AWG, Red

Documents:

[Drawing \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|------------------------|---|
| Product Family | Cable Assemblies |
| Series | 217521 |
| Application | Signal, Wire-to-Wire |
| Assembly Configuration | Pre-crimped Lead Only |
| Connector to Connector | Mizu-P25-to-Pigtail |
| Overview | Off-the-Shelf Pre-Crimped Leads |
| Product Name | Mizu-P25 |
| Type | Discrete Wire Assembly |
| UPC | 195842071988 |

Physical

| | |
|--------------------------------|----------------------|
| Cable Length | 300.00mm |
| Circuits (Loaded) | 1 |
| Color - Resin | Red |
| Gender | Female-Pigtail |
| Material - Metal | Phosphor Bronze |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Net Weight | 1.640/g |
| Single Ended | Yes |
| Termination Interface: Style | Crimp or Compression |
| Wire Insulation Diameter | 1.40-1.90mm |
| Wire Size AWG | 22 |
| Wire/Cable Type | N/A |

Electrical

| | |
|-------------------|------|
| Voltage - Maximum | 125V |
|-------------------|------|

Material Info

Reference - Drawing Numbers

| | |
|---------------|----------------|
| Sales Drawing | 2175211121-000 |
|---------------|----------------|



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[217521](#) Series