

sales@fibox.com

Product card: UL PC 150/100 XHG



Sample photo

Including: Base with PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Support items:

- [Product card \(PDF\)](#)
- [Dimensional drawing \(inch\)](#)
- [Dimensional drawing \(mm\)](#)
- [Cad-files \(registration needed\)](#)

Product nbr: 6013334
 Description: Enclosure, PC
 Remarks: Extra high base, grey cover
 Package: 4
 Unit: PCS
 Product group: MNX PC Enclosures
 EAN: 6418074061225
 SSTL number: 3435606
 Electric No. Denmark: 8212027873
 Electric No. Sweden: 6013334
 ETIM: EC000261 EC000261

Dimensions:

Length (mm): 180.0
 Width (mm): 130.0
 Height (mm): 100.0
 Length (inch): 7.1
 Width (inch): 5.1
 Height (inch): 3.9

Installation position:

Upright on a wall, pole or frame

Materials:

Material: Polycarbonate
 Base colour: RAL 7035 -light grey
 Cover screws material: Polyamide
 Cover colour: RAL 7035 -light grey
 Cover screws colour: Grey
 Gasket material: Polyurethane

Temperatures:

Temperature °C (short term): -40 ... 120 °C
 Temperature °C (continuous): -40 ... 80 °C
 Temperature °F (short term): -40 ... 250 °F
 Temperature °F (continuous): -40 ... 175 °F

Ratings:

Ingress Protection (EN 60529): IP66/IP67
 Impact Resistance (EN 62262): IK08
 Electrical insulation: Totally insulated
 Halogen free (DIN/VDE 0472, Part 815): 1
 UV resistance: UL 508
 Flammability Rating: UL 746C 5"
 Glow Wire Test (IEC 695-2-1) °C: 960
 NEMA Class: NEMA 1, 4, 4X, 6

Product is connected to following catalogs:

Fibox Enclosures : MNX : PC/ABS 150XH