

Product card: ARCA 403015 NO MP



Sample photo

Including: Cabinet base, door with PUR gasket, 3mm double bit lock(s) with key. 2-point locking system. Door guide included.

Support items:

- [Product card \(PDF\)](#)
- [Dimensional drawing \(mm\)](#)
- [Cad-files \(registration needed\)](#)

Product nbr: 8120006N
 Description: Cabinet, PC
 Remarks: Grey cover, 2-point locking, hinges on the long side
 Package: 1
 Unit: PCS
 Product group:
 EAN: 6418074079176
 SSTL number: 3423051
 Electric No. Denmark: 8212091045
 Electric No. Sweden: 2500112
 ETIM: EC000261 EC000261

Dimensions:	
Length (mm):	400
Width (mm):	300
Height (mm):	150
Length (inch):	15.7
Width (inch):	11.8
Height (inch):	5.9

Ratings:	
Ingress Protection (EN 60529):	IP66/67
Impact Resistance (EN 62262):	IK07/IK08
Electrical insulation:	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	1
UV resistance:	UL 508
Flammability Rating:	UL 508
Glow Wire Test (IEC 695-2-1) °C:	960
NEMA Class:	NEMA 4, 4X,

Materials:		Temperatures:	
Material:	Polycarbonate	Temperature °C (short term):	-40 ... 140 °C
Base colour:	RAL 7035 -light grey	Temperature °C (continuous):	-40 ... 80 °C
Cover screws material:	Stainless steel	Temperature °F (short term):	-40 ... 284 °F
Cover colour:	RAL 7035 -light grey	Temperature °F (continuous):	-40 ... 175 °F
Gasket material:	Polyurethane		