

**UL MNX UL PC 95/50 LT**



Sample photo

<b>Order symbol:</b>	UL PC 95/50 LT	<b>EAN:</b>	6418074057761
<b>Product nbr:</b>	6412932	<b>EI. number:</b>	
<b>Description:</b>	UL Enclosure, PC	<b>Finland:</b>	
<b>Remarks:</b>	Smoked transparent cover	<b>Electric No. Denmark:</b>	8212030828

Including: Base with PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		100	100	50	Ingress Protection (EN 60529): IP66/IP67
inch:		3.9	3.9	2.0	Impact Resistance (EN 62262): IK08
<b>Materials:</b>					Electrical insulation: Totally insulated
<b>Material:</b>		Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): 1
<b>Base colour:</b>		RAL 7035 -light grey			UV resistance: UL 508
<b>Cover screws material:</b>		Polyamide			Flammability Rating: UL 746C 5"
<b>Cover colour:</b>		Smoked grey			UL Type:
<b>Cover screws colour:</b>		Black			Glow Wire Test (IEC 695-2-1) °C: 960
<b>Gasket material:</b>		Polyurethane			<b>Certificates:</b>
<b>Temperatures:</b>					Underwriters Laboratories
<b>Temperature °C (short term):</b>		-40 ... 120 °C			SGS Fimko
<b>Temperature °C (continuous):</b>		-40 ... 80 °C			UL Canada
<b>Temperature °F (short term):</b>		-40 ... 250 °F			Gost R
<b>Temperature °F (continuous):</b>		-40 ... 175 °F			