

UL MNX UL PC 95/50 LG



Sample photo

Order symbol: UL PC 95/50 LG
Product nbr: 6412332
Description: UL Enclosure, PC
Remarks: Grey cover

EAN: 6418074057662
EI. number:
Finland:
Electric No. 8212030815
Denmark:

Including: Base with PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:				Rating:
	Length	Width	Height	
mm:	100	100	50	Ingress Protection (EN 60529): IP66/IP67
inch:	3.9	3.9	2.0	Impact Resistance (EN 62262): IK08
Materials:				Electrical insulation: Totally insulated
Material:	Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): 1
Base colour:	RAL 7035 -light grey			UV resistance: UL 508
Cover screws material:	Polyamide			Flammability Rating: UL 746C 5"
Cover colour:	RAL 7035 -light grey			UL Type:
Cover screws colour:	Grey			Glow Wire Test (IEC 695-2-1) °C: 960
Gasket material:	Polyurethane			Certificates:
Temperatures:				Underwriters Laboratories
Temperature °C (short term):	-40 ... 120 °C			SGS Fimko
Temperature °C (continuous):	-40 ... 80 °C			UL Canada
Temperature °F (short term):	-40 ... 250 °F			Gost R
Temperature °F (continuous):	-40 ... 175 °F			

