

Order symbol:	UL PC 200/175 XHT	EAN:	6418074057136
Product nbr:	6413929	EI. number:	
Description:	UL Enclosure, PC	Finland:	
Remarks:	Smoked transparent cover	Electric No. Denmark:	8212030721
		Electric No. Italy:	7352155U

Including: Base with PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		255	180	175	Ingress Protection (EN 60529): IP66/IP67
inch:		10.0	7.1	6.9	Impact Resistance (EN 62262): IK08
Materials:					Electrical insulation: Totally insulated
Material:		Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): 1
Base colour:		RAL 7035 -light grey			UV resistance: UL 508
Cover screws material:		Polyamide			Flammability Rating: UL 746C 5"
Cover colour:		Smoked grey			UL Type:
Cover screws colour:		Black			Glow Wire Test (IEC 695-2-1) °C: 960
Gasket material:		Polyurethane			
Temperatures:					Certificates:
Temperature °C (short term):		-40 ... 120 °C			Underwriters Laboratories
Temperature °C (continuous):		-40 ... 80 °C			SGS Fimko
Temperature °F (short term):		-40 ... 250 °F			UL Canada
Temperature °F (continuous):		-40 ... 175 °F			Gost R

