

**UL MNX UL PC 125/100 LG**



Sample photo

**Order symbol:** UL PC 125/100 LG  
**Product nbr:** 6412310  
**Description:** UL Enclosure, PC  
**Remarks:** Grey cover

**EAN:** 6418074014313  
**EI. number:**  
**Finland:**  
**Electric No.** 8212030187  
**Denmark:**  
**Electric No. Italy:** 7351050U

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:	Length	Width	Height	Rating:
<b>mm:</b>	130	130	100	Ingress Protection (EN 60529): IP66/IP67
<b>inch:</b>	5.1	5.1	3.9	Impact Resistance (EN 62262): IK08
<b>Materials:</b>				Electrical insulation: Totally insulated
<b>Material:</b>	Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): 1
<b>Base colour:</b>	RAL 7035 -light grey			UV resistance: UL 508
<b>Cover screws material:</b>	Polyamide			Flammability Rating: UL 746C 5"
<b>Cover colour:</b>	RAL 7035 -light grey			UL Type:
<b>Cover screws colour:</b>	Grey			Glow Wire Test (IEC 695-2-1) °C: 960
<b>Gasket material:</b>	TPE			<b>Certificates:</b>
<b>Temperatures:</b>				Underwriters Laboratories
<b>Temperature °C (short term):</b>	-40 ... 120 °C			SGS Fimko
<b>Temperature °C (continuous):</b>	-40 ... 80 °C			UL Canada
<b>Temperature °F (short term):</b>	-40 ... 250 °F			Gost R
<b>Temperature °F (continuous):</b>	-40 ... 175 °F			

