

MNX PCM 175/175 XG

Order symbol: PCM 175/175 XG
Product nbr: 6016343
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074011831
EI. number:
 Finland: 3413014
 Electric No. 8212026764
 Denmark:
 Electric No. Sweden: 6016343

Including: Base with metric knock-outs and TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:
mm:	180	180	175	MIN 15 DIN-15 Mounting rail
inch:	7.1	7.1	6.9	MIV 15 DIN-35 Mounting rail

Materials:

Material: Polycarbonate

Base colour: RAL 7035 -light grey

Cover screws material: Polyamide

Cover colour: RAL 7035 -light grey

Cover screws colour: Grey

Gasket material: TPE

Accessories:

FP A 175/180 Front plate (Aluminium)

HFP 180 Front plate hinge series

FP 22046 Wall fastening lug (4 pcs)

Temperatures:

Temperature °C (short term): -40 ... 120 °C

Temperature °C (continuous): -40 ... 80 °C

Temperature °F (short term): -40 ... 250 °F

Temperature °F (continuous): -40 ... 175 °F

Rating:

Ingress Protection (EN 60529): IP66/IP67

Impact Resistance (EN 62262): IK08

Electrical insulation: Totally insulated

Halogen free (DIN/VDE 0472, Part 815): 1

UV resistance: UL 508

Flammability Rating: UL 746C 5"

Glow Wire Test (IEC 695-2-1) °C: 960

NEMA Class: NEMA 1, 4, 4X, 6, 12, 13

Accessories:

MIV 175 Mounting plate (Galvanized steel)

Certificates:

SGS Fimko

