

UL MNX UL PC 100/100 HT



Sample photo

Order symbol: UL PC 100/100 HT
Product nbr: 6411903
Description: UL Enclosure, PC
Remarks: Smoked transparent cover

EAN: 6418074014535
EI. number:
 Finland:
 Electric No. 8212030019
 Denmark:
 Electric No. Italy: 7352030U

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

| Dimensions: | Length | Width | Height | Rating: |
|-------------------------------------|----------------------|-------|--------|--|
| mm: | 130 | 80 | 100 | Ingress Protection (EN 60529): IP66/IP67 |
| inch: | 5.1 | 3.1 | 3.9 | Impact Resistance (EN 62262): IK08 |
| Materials: | | | | Electrical insulation: Totally insulated |
| Material: | Polycarbonate | | | Halogen free (DIN/VDE 0472, Part 815): 1 |
| Base colour: | RAL 7035 -light grey | | | UV resistance: UL 508 |
| Cover screws material: | Polyamide | | | Flammability Rating: UL 746C 5" |
| Cover colour: | Smoked grey | | | UL Type: |
| Cover screws colour: | Black | | | Glow Wire Test (IEC 695-2-1) °C: 960 |
| Gasket material: | TPE | | | Certificates: |
| Temperatures: | | | | Underwriters Laboratories |
| Temperature °C (short term): | -40 ... 120 °C | | | SGS Fimko |
| Temperature °C (continuous): | -40 ... 80 °C | | | UL Canada |
| Temperature °F (short term): | -40 ... 250 °F | | | Gost R |
| Temperature °F (continuous): | -40 ... 175 °F | | | |

