

Product card: ARCA 302015 NO MP



Sample photo

Including: Cabinet base, door with PUR gasket, 3mm double bit lock(s) with key. 2-point locking system. Door guide included.

Support items:

[Product card \(PDF\)](#)

[Dimensional drawing \(mm\)](#)

[Cad-files \(registration needed\)](#)

Product nbr: 8120020N
 Description: Cabinet, PC
 Remarks: Grey cover, 1-point locking, hinges on the long side
 Package: 1
 Unit: PCS
 Product group:
 EAN: 6418074079312
 SSTL number: 3423117
 Electric No. 8212091184
 Denmark:
 Electric No. 2500109
 Sweden:
 ETIM: EC000261 EC000261

Dimensions:

| | |
|----------------|------|
| Length (mm): | 300 |
| Width (mm): | 200 |
| Height (mm): | 150 |
| Length (inch): | 11.8 |
| Width (inch): | 7.9 |
| Height (inch): | 5.9 |

| Ratings: | |
|--|-------------------|
| Ingress Protection (EN 60529): | IP66/67 |
| Impact Resistance (EN 62262): | IK07/IK08 |
| Electrical insulation: | Totally insulated |
| Halogen free (DIN/VDE 0472, Part 815): | 1 |
| UV resistance: | UL 508 |
| Flammability Rating: | UL 508 |
| Glow Wire Test (IEC 695-2-1) °C: | 960 |
| NEMA Class: | NEMA 4, 4X, |

| Materials: | | Temperatures: | |
|------------------------|----------------------|------------------------------|----------------|
| Material: | Polycarbonate | Temperature °C (short term): | -40 ... 140 °C |
| Base colour: | RAL 7035 -light grey | Temperature °C (continuous): | -40 ... 80 °C |
| Cover screws material: | Stainless steel | Temperature °F (short term): | -40 ... 284 °F |
| Cover colour: | RAL 7035 -light grey | Temperature °F (continuous): | -40 ... 175 °F |
| Gasket material: | Polyurethane | | |