

UL PICCOLO UL PC D 65 T



Sample photo

Order symbol: UL PC D 65 T
Product nbr: 8714007
Description: UL Enclosure, PC
Remarks: Transparent cover

EAN: 6418074038883
EI. number:
Finland:
Electric No. Denmark: 8212031102
Electric No. Italy: 7202030U

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:				Rating:
	Length	Width	Height	
mm:	170	80	65	Ingress Protection (EN 60529): IP66/IP67
inch:	6.7	3.1	2.6	Impact Resistance (EN 62262): IK08
Materials:				Electrical insulation: Totally insulated
Material:	Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): 1
Base colour:	RAL 7035 -light grey			UV resistance: UL 508
Cover screws material:	Polyamide			Flammability Rating: UL 746C 5"
Cover colour:	Clear transparent			UL Type:
Cover screws colour:	Grey			Glow Wire Test (IEC 695-2-1) °C: 960
Gasket material:	Polyurethane			Certificates:
Temperatures:				Underwriters Laboratories
Temperature °C (short term):	-40 ... 120 °C			SGS Fimko
Temperature °C (continuous):	-40 ... 80 °C			UL Canada
Temperature °F (short term):	-40 ... 250 °F			Gost R
Temperature °F (continuous):	-40 ... 175 °F			

PICCOLO 170x80x65-85

