

RoHS  
Compliant



## Specifications

### Designed of cable

Inner Conductor	: 7/0.2 ±0.005mm Strand CCA Ø0.6 ±0.01mm
Insulation	: PVC
Size of Insulation	: Ø1.1 ±0.1mm
Core Colour	: BK/YE/RD/BU/WH/GN/OG/BN
Drain Wire	: 7/0.2 ±0.005mm Strand CCA Ø0.6 ±0.01mm
Jacket	: PVC
Jacket Colour	: White
Jacket Size	: Ø5.4 ±0.5mm
Wall Thickness	: ≈0.7mm

### Electric data at 20°C

Conductor Resistance	: ≤141Ω/KM
Insulation Resistance	: ≥200MΩ*KM
Testing Voltage	: 50Hz 1 Min. wire/wire 50Hz 1min=800V
Temperature Range	: -10°C to +60°C

## Part Number Table

Description	Part Number
Multicore Cable, Screened, 8 Core, 100m	8CALMSCRCCA

**Important Notice** : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands  
Farnell.com/exclusive-brands  
Element14.com/exclusive-brands

# pro-POWER