


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1727673014](#)
Status: **Active**
Overview: [Mini-Fit Family Power Connectors](#)
Description: Mini-Fit Sigma Plug Housing, 4.20mm Pitch, Dual Row, Panel Mount, UL 94V-0, Glow-Wire Capable, 14 Circuits

Documents:

Drawing (PDF)	Packaging Specification 1727670002-PK-000 (PDF)
Product Specification 2029880002-PS-000 (PDF)	Test Summary 2131370002-TS-000 (PDF)
Product Specification 2131370000-PS-000 (PDF)	Datasheet (PDF)
Application Specification 2131370000-AS-000 (PDF)	RoHS Certificate of Compliance (PDF)



General

Product Family	Crimp Housings
Series	172767
Application	Power, Wire-to-Board, Wire-to-Wire
Overview	Mini-Fit Family Power Connectors
Product Name	Mini-Fit Sigma
UPC	195842073456

Physical

Circuits (maximum)	14
Color - Resin	Black
Gender	Plug
Glow-Wire Capable	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	4.850/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	2131370000-AS-000
Packaging Specification	1727670002-PK-000
Product Specification	2029880002-PS-000, 2131370000-PS-000
Sales Drawing	1727670002-SD-000
Test Summary	2131370002-TS-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[172767](#) Series

Mates With

Mini-Fit Sigma Receptacle Housing
[1727081014](#)

Use With

Mini-Fit TPA2/Sigma Male Terminal
[172765](#) , [203070](#) . Mini-Fit Sigma Retainer
[1727092007](#)