

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0153660153**
Status: **Active**
Overview: FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers
Description: 0.50mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 203.00mm Cable Length, Tin (Sn) Plating, 14 Circuits, with Shield

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification 153660001-000 \(PDF\)](#)

General

Product Family	Cable
Series	<u>15366</u>
Crimp Quality Equipment	Yes
Overview	<u>FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers</u>
Product Name	Premo-Flex FFC Jumper
UPC	193264621873

Physical

Cable Length	203.00mm
Circuits (Loaded)	14
Contact Layout Type	A (same side)
Material - Plating Mating	Tin
Packaging Type	Bag
Pitch - Mating Interface	0.50mm
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable


Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	N/A

Material Info

Reference - Drawing Numbers

Product Specification	153660001-000
Sales Drawing	153660001-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

15366 Series

Mates With

Easy-On FFC/FPC Connector [527451433](#) ,
[527461433](#) , [525591433](#) , [525591434](#)