

## TECHNICAL DATA SHEET

Part#: 6-ESD

Tweezers - Angulated Flat Sharp Point - Plastic  
Temperature resistant to 212°F / Prevents marring or scratching of delicate parts

The 6-ESD straight 4.75" 84° angled flat sharp pointed conductive plastic tweezer (10<sup>5</sup> ohms/sq) is temperature resistant to 212°F.

• Precision Level	★★
• Material	Plastic
• Surface Resistivity	10 <sup>5</sup> ohms/sq
• Shape	Angulated
• Tip Size	.05" x .04" (1.25mm x 1mm)
• Tip Angle	84°
• Tip Length	
• Body Width	.353" (8.83mm)
• Body Height	.089" (2.23mm)
• OAL	4.75" (118.75mm)
• Weight (OZ)	0.25
• UPC	662847002922
• Schedule B	8203.20.20.00
• ECCN	EAR99
• UNSPSC Code	27112105
• Country of Origin	China
• Group	Conductive Plastic

