

## TECHNICAL DATA SHEET

Part#: 159-RT-ET

**Tweezers - Replaceable Carbon Fiber .012" x .011" Tip - Ergo Grips**  
Will not scratch or marr delicate items

The 159-RT-RT soft replaceable tip tweezer is 5" long with .012" wide tips. The Carbofib<sup>™</sup> tips are a polymer based material with 30% carbon fibers added (conductive 10<sup>2</sup> ohms/sq). This tool includes an ergonomic handle. Carbofib<sup>™</sup> has very high rigidity, excellent tensile and flexural strength, fatigue and creep resistance, and temperature resistant to 249<sup>°</sup>F. Carbofib<sup>™</sup> is a polymer based material with 30% carbon fibers added (conductive 10<sup>2</sup> ohms/sq). The bodies are made of anti-magnetic Neverust<sup>®</sup> stainless steel (AISI 316L). They are excellent for handling delicate items. It features our Ergo-Tweeze<sup>®</sup> soft cushioned Anti-Static grips (10<sup>10</sup> ohms/sq surface resistivity), which also protect the user from heat.

- Precision Level                   ★★★
- Material                           Carbon Fiber Tips
- Surface Resistivity           10<sup>10</sup> ohms/sq
- Shape                             Straight
- Tip Size                         .012" x .011" (.3mm x .2mm)
- Tip Angle                        Straight
- Tip Length
- Body Width                     .393" (9.83mm)
- Body Height                    .06 (1.5mm)
- OAL                               6" (150mm)
- Weight (OZ)                    1
- UPC                               662847014505
- Schedule B                     8203.20.20.00
- ECCN                             EAR99
- UNSPSC Code                 27112105
- Country of Origin            Italy
- Group                            Carbon Fiber

