

TECHNICAL DATA SHEET

Part#: 36PH

Hemostats - 5" 25°Curved - SS - Vinyl Coated Handle
Ideal for clamping parts for inspection

The 36PH stainless steel locking hemostat with 25°curved serrated jaws has vinyl-coated handles. The overall length is 5".

• Precision Level	★★
• Material	SS (AISI 440)
• Surface Resistivity	Insulative
• Shape	Curved
• Tip Size	
• Tip Angle	25°
• Tip Length	
• Body Width	0.26" (6.5mm)
• Body Height	0.172"(4.3mm)
• OAL	5" (125mm)
• Weight (OZ)	2
• UPC	662847003851
• Schedule B	9018.90.80.00
• ECCN	EAR99
• UNSPSC Code	42151685
• Country of Origin	Pakistan
• Group	Curved - Vinyl Handles

