

TECHNICAL DATA SHEET

Part#: 15A-RW-PB

Tweezers - 3 Star Cutting - 15A-RW Series - Carbon Steel - Parallel Blade
General purpose cutting of small wires or flashing. The parallel blades allow cutting along the entire length of the blade.

The 15A-RW-PB 70° angulated round tip cutting tweezer is ideal for general purpose cutting of soft wire up to 0.010". The cutting blade is much shorter than the 15A-GW and the top of the head has been rounded for better visibility. The parallel blades afford cutting along any point on the blades.

| | |
|-----------------------|--|
| • Precision Level | ★★★ |
| • Material | Carbon Steel |
| • Surface Resistivity | 10 ⁵ -10 ⁶ ohms/sq |
| • Shape | Angulated |
| • Tip Size | .095" (2.38mm) |
| • Tip Angle | 70° |
| • Tip Length | |
| • Body Width | 0.393" (9.83mm) |
| • Body Height | .10" (2.50mm) |
| • OAL | 4.5" (112.5mm) |
| • Weight (OZ) | 1.5 |
| • UPC | 662847010415 |
| • Schedule B | 8203.20.20.00 |
| • ECCN | EAR99 |
| • UNSPSC Code | 27112105 |
| • Country of Origin | Switzerland |
| • Group | Relieved Round Head (15A-RW) |

