

TECHNICAL DATA SHEET

Part#: 15A-GW-S

Tweezers - 3 Star Cutting - 15A-GW Series - SS
Designed for general purpose cutting in a cleanroom environment.

The 15A-GW-S 70° angulated tip cutting tweezer is ideal for general purpose cutting of soft wire up to 0.010". This tool is considered a tip cutter in that the blades meet most predominately at the tip. All of the force applied to the tweezer gets transferred to the points. This tool is stainless steel, with no coating and therefor MEDICAL GRADE.

• Precision Level	★★★
• Material	SS (AISI 440)
• Surface Resistivity	Conductive
• Shape	Angulated
• Tip Size	.215" (5.38mm)
• Tip Angle	70°
• Tip Length	
• Body Width	0.393" (9.83mm)
• Body Height	.10" (2.50mm)
• OAL	4.5" (112.5mm)
• Weight (OZ)	1.5
• UPC	662847003370
• Schedule B	8203.20.20.00
• ECCN	EAR99
• UNSPSC Code	27112105
• Country of Origin	Switzerland
• Group	Standard Head (15A-GW)

