

## TECHNICAL DATA SHEET

Part#: 35A-ESD

**Tweezers - Straight Flat Point -- Plastic**  
Ideal for applications requiring heat

The 35A-ESD straight 4.5" wide point (1/4") conductive plastic tweezer (10<sup>5</sup> ohms/sq) is temperature resistant to 212°F.

• Precision Level	★★
• Material	Plastic
• Surface Resistivity	10 <sup>5</sup> ohms/sq
• Shape	Straight
• Tip Size	.24" x .005" (6mm x .005")
• Tip Angle	Straight
• Tip Length	
• Body Width	.364" (9.1mm)
• Body Height	.082" (2.05mm)
• OAL	4.5" (112.5mm)
• Weight (OZ)	0.25
• UPC	662847003783
• Schedule B	8203.20.20.00
• ECCN	EAR99
• UNSPSC Code	27112105
• Country of Origin	China
• Group	Conductive Plastic

