

TECHNICAL DATA SHEET

Part#: 15A-RW-S

Tweezers - 3 Star Cutting - 15A-RW Series - SS

Designed for general purpose cutting in a cleanroom environment.

The 15A-RW-S 70° angulated round tip cutting tweezer is ideal for general purpose cutting of soft wire up to 0.010". The cutting blade is much shorter than the 15A-GW and the top of the head has been rounded for better visibility. This tool is made of Stainless Steel i.e. MEDICAL GRADE.

• Precision Level	★★★
• Material	SS (AISI 440)
• Surface Resistivity	Conductive
• Shape	Angulated
• Tip Size	.28" (7mm)
• Tip Angle	70°
• Tip Length	
• Body Width	0.393" (9.83mm)
• Body Height	.10" (2.50mm)
• OAL	4.5" (112.5mm)
• Weight (OZ)	1.5
• UPC	662847003424
• Schedule B	8203.20.20.00
• ECCN	EAR99
• UNSPSC Code	27112105
• Country of Origin	Switzerland
• Group	Relieved Round Head (15A-RW)

