

## TECHNICAL DATA SHEET

Part#: 15A-GW-PB

Tweezers - 3 Star Cutting - 15A-GW Series - Carbon Steel - Parallel Blade  
Designed for general purpose cutting of small wires or flashing. The parallel blades allow cutting along the entire length of the blade.

The 15A-GW-PB 70° angulated tip cutting tweezer is ideal for general purpose cutting of soft wire up to 0.010". The overall length is 4.5". It is made of carbon steel with flame hardened edges. It features parallel cutting blades, which allow cutting at any point on the cutting blades.

• Precision Level	★★★
• Material	Carbon Steel
• Surface Resistivity	10 <sup>5</sup> -10 <sup>6</sup> ohms/sq
• Shape	Angulated
• Tip Size	.215" (5.38mm)
• Tip Angle	70°
• Tip Length	
• Body Width	0.393" (9.83mm)
• Body Height	.10" (2.50mm)
• OAL	4.5" (112.5mm)
• Weight (OZ)	1.5
• UPC	662847010392
• Schedule B	8203.20.20.00
• ECCN	EAR99
• UNSPSC Code	27112105
• Country of Origin	Switzerland
• Group	Standard Head (15A-GW)

