

TECHNICAL DATA SHEET

Part#: 15A-GW-M

Tweezers - 3 Star Cutting - 15A-GW Series - Carbon Steel - Medical Grade
Designed for general purpose cutting of small wires or flashing. The epoxy coating has been removed to prevent contamination.

The 15A-GW-M 70°angulated tip cutting tweezer is ideal for general purpose cutting of soft wire up to 0.010". This tool is considered a tip cutter in that the blades meet most predominately at the tip. All of the force applied to the tweezer gets transferred to the tips. The 'M' signifies that the tool is MEDICAL GRADE.

• Precision Level	★★★
• Material	Carbon Steel
• Surface Resistivity	Conductive
• Shape	Angulated
• Tip Size	.215" (5.38mm)
• Tip Angle	70°
• Tip Length	
• Body Width	0.393" (9.83mm)
• Body Height	.10" (2.50mm)
• OAL	4.5" (112.5mm)
• Weight (OZ)	1.5
• UPC	662847003356
• Schedule B	8203.20.20.00
• ECCN	EAR99
• UNSPSC Code	27112105
• Country of Origin	Switzerland
• Group	Standard Head (15A-GW)

